

One unit to both cure and whiten



BlueLEX

Cordless LED Curing Light

GT-1200W

MONITEX

BlueLEX GT-1200W

Cordless LED Curing Light

BlueLex GT-1200W combines the power and functionality of GT-1200, with an additional selection of a whitening mode to use in combination with the provided whitening arch. This not only allows users to quickly cure resin-based composites, but also provides whitening treatments when used in conjunction with whitening gels.



Bleaching Arch Included




3 Curing Modes

1 | Full Power Mode

Full power for optimal high speed polymerization.

Curing Cycle Default 8 secs (adjustable)



2 | Whitening Mode

15 minute whitening cure at 70% power.


Curing Cycle Default 15 mins



3 | Pulse Mode

Unit turns on and off every half second to reduce heat production.

Curing Cycle Default 20 secs



Specifications:

- LED Lamp 5 W
- Light Intensity 1,200 mW/cm² and up
- Wavelength Range 420~490 nm (peaks at 455~465 nm)
- Fiber-optic Probe Ø10~Ø8mm, autoclavable up to 132°C
- Handpiece Dimensions 210(L) x 43(W) x 43(H) mm
- Handpiece Weight 175 g
- Charger Stand Dimensions 192(L) x 97(W) x 65(H) mm
- Charger Stand Weight 130 g
- Power Input AC 100~240V, 50/60 Hz
- Power Output DC 9V $\bar{\bar{=}}$ 1.3A

MONITEX INDUSTRIAL CO., LTD

5F, 70, Sec. 1, Guangfu Rd., Sanchong Dist., New Taipei City 24158, TAIWAN

TEL: + 886 2 29993869 FAX: + 886 2 29993647

Email: monitex@monitex.com.tw

www.monitex.com.tw

